

MPEG4 Restricted Simple Profile Decoder (v01.00.00) on DM365

FEATURES

- eXpressDSP™ Digital Media (XDM 1.0 IVIDENC2) interface and IRES compliant
- Validated on DM365 EVM with Monta Vista® Linux® 5.0
- MPEG4 simple profile levels 0, 1, 2 and 3 are supported with the following limitations:
 - No support for 4 MV
 - No support for MV ranges beyond -32 to 31
 - No support for Data partitioning (DP) and Reversible VLCs (RVLCs)
- Decodes the following formats:
 - VGA (640 x4 80)
 - D1 (720 x 480)
 - 720P (1280 x 720)
 - SXVGA (1280 x 960)
- Half Pel Interpolation (HPI) for motion estimation supported
- One motion vector encoding for motion estimation (1MV/MB) with (-32, +31) half pel search range supported
- Streams with DC and AC prediction supported
- Streams with Resync Marker (RM) supported
- Streams with Short Video Header (SVH) supported
- YUV 4:2:2 interleaved data as an output supported
- YUV 4:2:0 semi-planar (NV12 format, that is, Y planar, Cb Cr interleaved) data as an output supported
- Display width can be greater than the image width.
- Supports rotation (90, 180 and 270 degrees) integrated with the Decoder for certain image formats such as QVGA (320x240), VGA (640x480), 720P (1280x720), and SXVGA (1280x960). Also supports rotation of 240x320 (rotated QVGA) and 480x640 (rotated VGA)
- Unrestricted Motion Vectors (UMV) supported
- Decodes all DM365 encoded streams
- Decodes streams of VBR, CBR, and CVBR rate control
- Frame level re-entrancy supported
- Multi-instance of MPEG4 Decoder, and single/multi instance of MPEG4 Decoder with other DM365 codecs supported
- Decodes only those streams encoded with the DM365 MPEG4 Encoder.
- This decoder does not support the following:
 - Video packet resynchronization
 - Header extension code (HEC)
 - AC prediction for varying Qp (rateFix = 0)
 - Arbitrary width and height.
 - Image width as multiple of 16 and height as multiple of 16 supported
 - Image width below 160 and 192 for YUV 422ILE and YUV 420SP format respectively is not supported
 - Decoding of 720x1280 (rotated 720P) and 960x1280 (rotated SXVGA) formats

DESCRIPTION

MPEG4 is the ISO/IEC recommended standard for video compression. This version of the MPEG4 Simple Profile decoder is a restricted decoder. It can only decode streams encoded by DM365 MPEG4 Encoder. It is validated on DM365 EVM with Monta Vista Linux 5.0.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

eXpressDSP is a trademark of Texas Instruments.

Linux is a registered trademark of Linus Torvalds.

Monta Vista is a registered trademark of MontaVista Software, Inc.

All other trademarks are the property of their respective owners.

Performance Summary

This section describes the performance of the MPEG4 Restricted Simple Profile Decoder on DM365 EVM.

Table 1. Configuration Table

| CONFIGURATION | ID |
|---|--------------------|
| MPEG4 simple profile, I/D Cache Enabled Output Format: XDM_YUV_420SP Rotation 0 ME 31 UMV OFF | MPEG4_DEC_01 |
| MPEG4 simple profile, I/D Cache Enabled Output Format: XDM_YUV_422ILE Rotation 0 ME 31 UMV OFF | MPEG4_DEC_02 |
| MPEG4 simple profile (SVH Mode), I/D Cache Enabled Output Format: XDM_YUV_422ILE Rotation 0 ME 31 UMV OFF | MPEG4_DEC_03 (SVH) |

Performance Measurement Procedure

- Measured with program memory and I/O buffers in external memory, I/D cache enabled, ARM @297 MHz, MJCP @243 MHz, DDR @243 MHz, Monta Vista Linux 5.0
- DVTB is used to measure the performance numbers in this Datasheet.
- The process time is measured across algActivate/process/algDeactivate function call using gettimeofday() utility of linux.
- NFS File system is used as an environment in performance measurement.
- To avoid the impact of file I/O operation in performance measurement, file write operation is disabled and checksum calculation is included after fread() function to make sure file read has really completed before process call.
- After rebooting the board, codec binary must be executed at least once before start of performance measurement.

Note: Frame decode load can be divided in ARM load and MJCP load. ARM is idle during MJCP processing, and can be utilized to execute any other program in different thread during this time.

Table 2. Cycles Information for MPEG4_DEC_01

| INPUT NAME | RESOLUTION | PERFORMANCE STATISTICS (MEGA CYCLES PER SECOND) ⁽¹⁾ | | | | | |
|------------|--------------------------|--|------------------|--------|------------------|------------------|--------|
| | | AVERAGE | | | PEAK | | |
| | | ARM926 PER FRAME | DECODE PER FRAME | FPS | ARM926 PER FRAME | DECODE PER FRAME | FPS |
| BUS | CIF (352x288) @512kbps | 0.53 | 1.13 | 262.81 | 0.58 | 1.18 | 252.53 |
| Coastguard | VGA (640x480) @3mbps | 0.53 | 2.26 | 131.46 | 0.61 | 2.34 | 127.15 |
| Football | D1 (720x480) @4mbps | 0.53 | 3.01 | 98.54 | 0.58 | 3.07 | 96.85 |
| Stockholm | 720p (1280x720) @8mbps | 0.52 | 5.64 | 52.70 | 0.57 | 5.68 | 52.25 |
| Pedestrian | SXVGA (1280x960) @10mbps | 0.53 | 7.34 | 40.47 | 0.59 | 7.40 | 40.16 |

(1) Average and peak MCPS values may vary by +/-5%.

Table 3. Cycles Information for MPEG4_DEC_02

| INPUT NAME | RESOLUTION | PERFORMANCE STATISTICS (MEGA CYCLES PER SECOND) ⁽¹⁾ | | | | | |
|------------|--------------------------|--|------------------|--------|------------------|------------------|--------|
| | | AVERAGE | | | PEAK | | |
| | | ARM926 PER FRAME | DECODE PER FRAME | FPS | ARM926 PER FRAME | DECODE PER FRAME | FPS |
| BUS | CIF (352x288) @512kbps | 0.53 | 1.12 | 265.18 | 0.58 | 1.17 | 252.97 |
| Coastguard | VGA (640x480) @3mbps | 0.52 | 2.23 | 132.94 | 0.62 | 2.33 | 127.36 |
| Football | D1 (720x480) @4mbps | 0.53 | 3.00 | 99.15 | 0.57 | 3.04 | 97.72 |
| Stockholm | 720p (1280x720) @8mbps | 0.52 | 5.60 | 53.04 | 0.56 | 5.64 | 52.65 |
| Pedestrian | SXVGA (1280x960) @10mbps | 0.53 | 7.28 | 40.79 | 0.60 | 7.36 | 40.36 |

(1) Average and peak MCPS values may vary by +/-5%.

Table 4. Cycles Information for MPEG4_DEC_03

| INPUT NAME | RESOLUTION | PERFORMANCE STATISTICS (MEGA CYCLES PER SECOND) ⁽¹⁾ | | | | | |
|------------|------------------------|--|------------------|--------|------------------|------------------|--------|
| | | AVERAGE | | | PEAK | | |
| | | ARM926 PER FRAME | DECODE PER FRAME | FPS | ARM926 PER FRAME | DECODE PER FRAME | FPS |
| Foreman | CIF (352x288) @512kbps | 0.54 | 1.14 | 260.62 | 0.63 | 1.22 | 243.01 |
| ICE | 2CIF (704x576) @4mbps | 0.55 | 2.82 | 105.19 | 0.60 | 2.87 | 103.43 |

(1) Average and peak MCPS values may vary by +/-5%.

Note:

- The values in Table 2, 3, and 4 are as measured on the ARM 926 side. These are the actual cycles as seen from the host on the DM365 EVM board and will be close to cycles seen on the final system (for average case).
- ARM926 represents mega cycles per frame spend on ARM926.
- Decode frame time is the time seen from ARM926 only. Since most of the processing happens at MJCP, the active load on ARM926 is the value mentioned in ARM926 column. Decode frame time has no connection with MJCP running at 243 MHz.
- All values are collected (both average and peak) at frame-level processing.
- They are measured with Linux without any system traffic.

Table 5. Memory Statistics

| RESOLUTION | MEMORY STATISTICS (IN BYTES) | | | | | |
|------------------|------------------------------|-------------|----------|----------|-------|---------|
| | PROGRAM MEMORY | DATA MEMORY | | | | TOTAL |
| | | CONSTANT | INTERNAL | EXTERNAL | STACK | |
| SXVGA (1280x960) | 101562 | 4274 | 0 | 4154648 | 8192 | 4268676 |
| 720P (1280x720) | 101562 | 4274 | 0 | 3186968 | 8192 | 3300996 |
| D1 (720x480) | 101562 | 4274 | 0 | 1305368 | 8192 | 1419396 |
| VGA (640x480) | 101562 | 4274 | 0 | 1174808 | 8192 | 1288836 |
| CIF (352x288) | 101562 | 4274 | 0 | 465176 | 8192 | 579204 |

Table 6. Usage of External Memory through CMEM

| BUFFER | SIZE |
|-----------------------------|-----------------------------|
| Input Buffer ⁽¹⁾ | frameSize ⁽²⁾ *2 |

(1) Input buffer size is theoretical size based on 1:1 compression. Actual input size will be lower than this.

(2) frameSize = (Width * Height).

Table 6. Usage of External Memory through CMEM (continued)

| BUFFER | SIZE | |
|----------------------|-------------|--|
| Output Buffer | YUV_422_ILE | Buffer1: frameSize*2 |
| | YUV_420_SP | Buffer1: frameSize Buffer2: frameSize/2 |
| External Data Memory | memTab[0] | 11928 |
| | memTab[1] | 3* frameSize_padded ⁽³⁾ |
| | memTab[2] | 5760 Bytes |
| | memTab[3] | 8192 Bytes |

(3) $\text{frameSize_padded} = ((\text{Width} + 64) * (\text{Height} + 64))$

Notes

- The entire MJCP is a video resource and is used by the codec
- DMA configuration

Table 7. DMA Configuration

| TC Q's | TC 0 | TC 1 | TC 2 | TC 3 | TOTAL |
|---------------|---------------------|------------------------------------|-------------------|-------------------|--------|
| Usage | Reserved for system | Used by codec | Not used by codec | Not used by codec | - |
| Priority | 0 | Not touched by codec (Default – 7) | - | - | - |
| EDMA Channels | 0 | 31 | 0 | 0 | 31/64 |
| PaRAM Entries | 0 | 47 | 0 | 0 | 47/256 |
| QDMA Channels | 0 | 0 | 0 | 0 | 0/8 |

- The MJCP/EDMA resources are acquired using a generic resource manager known as Framework component. See *MPEG4 Restricted Simple Profile Decoder on DM365 User's Guide* for details.
- Code placement
All the algorithm code are placed in external memory. The performance quoted is not sensitive to algorithm code placement.

References

- ISO/IEC 14496-2:2004, Information technology -- Coding of audio-visual objects -- Part 2: Visual (Approved in 2004-05-24)
- *MPEG4 Restricted Simple Profile Decoder on DM365 User's Guide* (literature number: SPRUEV2)

Glossary

| TERM | DESCRIPTION |
|-----------|---|
| Constants | Elements that go into .const memory section |
| Scratch | Memory space that can be reused across different instances of the algorithm |
| Shared | Sum of Constants and Scratch |
| Instance | Persistent-memory that contains persistent information - allocated for each instance of the algorithm |

Acronyms

| ACRONYM | DESCRIPTION |
|---------|--|
| CBR | Constant Bit Rate |
| CIF | Common Intermediate Format |
| CVBR | Constrained Variable Bit Rate |
| DP | Data Partitioning |
| EVM | Evaluation Module |
| HPI | Half Pel Interpolation |
| MJCP | MPEG4-JPEG Co-Processor |
| MV | Motion Vector |
| NV12 | YUV 420 format with Y plane and CbCr plane |
| QP | Quantization Parameter |
| QCIF | Quarter Common Intermediate Format |
| QVGA | Quarter Video Graphics Array |
| RVLC | Reversible Variable Length Coding |
| SQCIF | Sub Quarter Common Intermediate Format |
| SSE | Sum of Square of Errors |
| SXVGA | Super eXtended Graphics Array |
| UMV | Unrestricted Motion Vectors |

PRODUCT PREVIEW

| ACRONYM | DESCRIPTION |
|----------------|-----------------------------|
| VBR | Variable Bit Rate |
| VGA | Video Graphics Array |
| VUI | Video Usability Information |
| XDM | eXpressDSP Digital Media |

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

| | |
|-----------------------------|--|
| Amplifiers | amplifier.ti.com |
| Data Converters | dataconverter.ti.com |
| DLP® Products | www.dlp.com |
| DSP | dsp.ti.com |
| Clocks and Timers | www.ti.com/clocks |
| Interface | interface.ti.com |
| Logic | logic.ti.com |
| Power Mgmt | power.ti.com |
| Microcontrollers | microcontroller.ti.com |
| RFID | www.ti-rfid.com |
| RF/IF and ZigBee® Solutions | www.ti.com/lprf |

Applications

| | |
|--------------------|--|
| Audio | www.ti.com/audio |
| Automotive | www.ti.com/automotive |
| Broadband | www.ti.com/broadband |
| Digital Control | www.ti.com/digitalcontrol |
| Medical | www.ti.com/medical |
| Military | www.ti.com/military |
| Optical Networking | www.ti.com/opticalnetwork |
| Security | www.ti.com/security |
| Telephony | www.ti.com/telephony |
| Video & Imaging | www.ti.com/video |
| Wireless | www.ti.com/wireless |

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2009, Texas Instruments Incorporated