

JPEG Baseline Profile Encoder (v02.02.02) on C66x

FEATURES

- eXpressDSP™ Digital Media (XDM 1.0 IIMGENC1) interface compliant
- Validated on TMS320C6678 EVM
- Baseline sequential mode for interleaved data formats (single scan) supported
- Multiple scans for planar formats YUV420, YUV411, YUV422, and YUV444 supported
- Arbitrary image size supported
- Maximum of three scans supported
- Comment insertion into the JPEG header supported
- Frame-based mode encoding supported
- Standard JPEG header included and JFIF style header is also supported
- Huffman tables are hard-coded and built into the application at compile-time
- Custom quantization tables supported
- Quantization tables are fixed with a quality factor (1 – 100) adjusting the quantization level
- Encoding images with pixel resolution more than 8 bits per pixel not supported
- Thumbnail supported
- DRI Marker insertions in the compressed bit-stream supported
- Insertion of application data APP0, APP1 and APP13 supported
- Supports ELF ABI Format

DESCRIPTION

JPEG Encoder accepts planar image data in YUV 4:2:0, YUV 4:1:1, YUV 4:2:2, and YUV 4:4:4 formats. It accepts interleaved image data in YUV 4:2:2 format and grayscale input. This codec is developed using Code Composer Studio 5.2.1.00018 and code generation tools version 7.4.0.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

eXpressDSP is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

PRODUCT PREVIEW information concerns products in the formative or design phase of development. Characteristic data and other specifications are design goals. Texas Instruments reserves the right to change or discontinue these products without notice.

Copyright © 2013, Texas Instruments Incorporated

Performance Summary

This section describes the performance of the JPEG Baseline Profile Encoder on TMS320C6678 EVM.

Table 1. Configuration Table

CONFIGURATION	ID
Normal configuration (4:2:2 interleaved Input and 4:2:2 output)	JPEG_ENC_001 ⁽¹⁾

(1) This configuration of JPEG Encoder does not require DMA resource. Default cache configuration (L1D cache: 32 K-bytes, L1P cache:32 K-bytes, L2 cache: 128 K-bytes).

Table 2. Cycles Information – Profiled on TMS320C6678 EVM with Code Generation Tools Version 7.4.0

CONFIGURATION ID	PERFORMANCE STATISTICS (IN CYCLES PER PIXEL) ⁽¹⁾		
	TEST DESCRIPTION	AVERAGE	PEAK ⁽²⁾
JPEG_ENC_001	Measured on input file, Input_422.yuv with frame size 768 x 512 at 10:1 compression ratio with DRI disabled	12.96	None

(1) Measured with program memory in MSMCSRAM, stack in L2SRAM and I/O buffers in ERAM.

(2) Peak value is not calculated for this version of JPEG Encoder.

Note:

- Default cache configuration (L1D cache: 32 K-bytes, L1P cache: 32 K-bytes, L2 cache: 128K-bytes).
- If TMS320C6678 EVM runs at 1000 MHz, then Mega pixels/sec will be 1000 MHz/Cycles per pixel = 1000 MHz/15 = 66.66 Mega pixels/second.
- The Cycles consumed by the Encoder will increase when DRI is enabled (especially, if DRI interval = 1).

Table 3. Memory Statistics - Generated with Code Generation Tools Version 7.4.0

CONFIGURATION ID	MEMORY STATISTICS ⁽¹⁾				TOTAL
	PROGRAM MEMORY	DATA MEMORY			
		INTERNAL	EXTERNAL	STACK	
JPEG_ENC_001	38.5	0	173.65	8	220.15

(1) All memory requirements are expressed in kilobytes (1K-byte = 1024 bytes).

Table 4. Internal Data Memory Split-Up

CONFIGURATION ID	DATA MEMORY - INTERNAL ⁽¹⁾		INSTANCE ⁽²⁾
	SHARED		
	CONSTANTS	SCRATCH	
JPEG_ENC_001	0	0	0

(1) All memory requirements are expressed in kilobytes.

(2) Does not include I/O buffers.

Table 5. External Data Memory Split-Up

CONFIGURATION ID	DATA MEMORY - EXTERNAL ^{(1) (2) (3)}		INSTANCE
	SHARED		
	CONSTANTS	SCRATCH	
JPEG_ENC_001	4.1	164.75	4.8

(1) All memory requirements are expressed in kilobytes.

(2) Measured with values Thumbnail Width =200 and Thumbnail Height =200.

(3) Constants are mapped to MSMCSRAM.

Notes

- Total data memory for N non pre-emptive instances = Constants + Scratch + N * (Instance + I/O buffers + Stack)

References

- TMS320 DSP Algorithm Standard Rules and Guidelines (literature number SPRU352)
- *JPEG Baseline Profile Encoder(v02.02.00) on C66x (on C6678EVM) User's Guide* (SPRUHB2)

Glossary

TERM	DESCRIPTION
Constants	Elements that go into .const memory section
Scratch	Memory space that can be reused across different instances of the algorithm
Shared	Sum of Constants and Scratch
Instance	Persistent-memory that contains persistent information - allocated for each instance of the algorithm

Acronyms

ACRONYM	DESCRIPTION
ABI	Application Binary Interface
ELF	Executable and Linkable Format
EXIF	Exchangeable Image File Format
JFIF	Joint File Interchange Format
JPEG	Joint Photographic Experts Group
XDM	eXpressDSP Digital Media

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive & Transportation	www.ti.com/automotive
Communications & Telecom	www.ti.com/communications
Computers & Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energyapps
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics & Defense	www.ti.com/space-avionics-defense
Video & Imaging	www.ti.com/video

TI E2E Community e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright© 2013, Texas Instruments Incorporated